

# MicroVantage™ MDP Series

Absolute-Rated (99.98%) High Performance Pleated Polypropylene Filter Cartridges

# MicroVantage Ultra Premium Filter Series



- Absolute-Rated Beta 5000 (99.98%) retention efficiency
- 7.0 square feet (0.65 m<sup>2</sup>) of media surface area per 10" length
  - Maximum throughput and particle retention
  - Longer service life reduces maintenance costs
- 100% polypropylene construction offers wide range of chemical compatibility
- Rigid, molded cage provides greater structural integrity
- Gradient, fixed pore structure increases dirt-holding capacity and resists unloading under high differential pressure
- Manufactured in state-of-the-art white room for high purity
- Complies with Food & Drug Administration's CFR criteria for food & beverage contact
- Meets USP Class VI Biological Test for plastics
- Various end cap configurations available to fit existing housings
- Produced in 10" segments for maximum strength and pleat protection
- Optional preflushed cartridges available for electronic and pharmaceutical applications

## Applications

RO Prefilters	Food & Beverage
Process Water	Bottled Water
Plating Solutions	Microelectronics
Chemicals	Paint/Inks

## Specifications & Operating Parameters

**Pore Sizes** 0.2, 0.45, 1.0, 3.0, 5.0, 10.0, 20.0, 30.0, 40.0, 50.0 microns

**Nominal Lengths** 9.75" (24.7 cm), 10" (25.4 cm), 20" (50.8 cm), 30" (76.2 cm), 40" (101.6 cm)

**Outside Diameter** 2.67" (6.78 cm)

**Inside Diameter** 1.0" (2.54 cm)

**Media Surface Area** 7.0 sq. ft. (0.65 m<sup>2</sup>) per ten inches in length

### Gaskets/O-rings

Silicone, Buna N, EPR, Viton, Teflon Encapsulated  
Viton (o-rings only)

### Materials of Construction

Filter Media: Polypropylene  
Outer Cage / Core / End Caps: Polypropylene

**Maximum Operating Temperature** 176°F ( 80°C)

**Recommended Change-out Differential Pressure**  
35 psid (2.4 bar)

**Maximum Differential (Collapse) Pressure**  
75 psid @ 70°F (5.2 bar @21°C), 40 psid @176°F (2.8 bar @ 80°C)


### Sanitization and Sterilization

Hot water at 175°F (80°C) at 5 psid for 30 minutes  
In-line steam at 257°F (125°C) @ 1 psid (0.07 bar) for 30 minutes  
Autoclavable at 257°F (125°C) for 30 minutes

### FDA and USP Compliance

All filters are manufactured of virgin polypropylene materials. All materials comply with FDA requirements for food contact per CFR Title 21 174.5, 177.1520 and 177.1630. All Components meet USP Class VI Plastics biological reactivity tests.

## Flow vs. Pressure Drop



This chart represents typical water flow per 10" cartridge length. The test fluid is water at ambient temperature. Extrapolation for multiple elements tends to be linear, but as flows increase the  $\Delta P$  of the housing becomes more apparent

## Filter Removal Efficiency

PORE SIZE	BETA 5000 99.98%	BETA 100 99%	BETA 50 98%
0.2 micron	0.20	0.10	0.05
0.45 micron	0.45	0.30	0.20
1.0 micron	1.0	0.65	0.35
3.0 micron	3.0	2.5	2.0
5.0 micron	5.0	4.0	3.0
10.0 micron	10.0	8.0	7.0
20.0 micron	20.0	17.0	15.0
30.0 micron	30.0	26.0	21.0
40.0 micron	40.0	34.0	28.0
50.0 micron	50.0	42.0	36.0

## Ordering Guide (Example: MDP1.0-10S3E)

MDP	1.0	10	–	S3	–	E	–
PRODUCT CODE	MICRON	LENGTH	END CAP CONFIGURATION		GASKET / O-RING		OPTION
MDP	0.2 0.45 1.0 3.0 5.0 10.0 20.0 30.0 40.0 50.0	9.75" 10" 20" 30" 40"	S1 = DOE S3 = 222 w/ Fin End S4 = 222 w/ Flat End S5 = 226 w/ Fin End S6 = 226 w/ Flat End S7 = Internal O-ring with Recessed Plug S9 = Internal O-ring on both ends		B = Buna N E = EPDM S = Silicone V = Viton T = Teflon encapsulated Viton (O-ring only)		F = Flushed with 18megohm DI water (Constructed with 10" modules)

## Filter Housings

Shelco manufactures a full line of filter housings. From our rugged single cartridge housings to our heavy duty multi-cartridge housings. Shelco is the perfect choice for your filtration solutions.



### Shelco Filters

100 Bradley Street  
Middletown, CT 06457 USA

Tel: 800-543-5843 / Fax: 860-854-6120 / E-mail: [info@shelco.com](mailto:info@shelco.com)

MicroSentry™, MicroVantage™, Shelco Filters® and the Shelco logo are registered trademarks of the Tinny Corporation. Shelco Filters is a division of the Tinny Corporation.